Rittal - The System.

Faster – better – everywhere.





AX 1003.000 Basic enclosure AX, stainless steel

State: 2025-11-15 (Source: rittal.com/ca-en)




AX 1003.000 - Basic enclosure AX, stainless steel

The robust stainless steel housings feature an integrated cam system that allows for extensive system expansion without drilling, quickly and securely.







Features

Model No.	AX 1003.000
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s), swing angle 130°
	Mounting panel
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 1
	NEMA 3R
	NEMA 4
	NEMA 4X
	NEMA 12
Protection category IP to EN 60 529	IP 66

© Rittal 2025

Features

Type 1 Type 3R Type 4 Type 4X Type 12
IK10
Width: 300 mm Height: 300 mm Depth: 210 mm
1.5 mm
1.25 mm
2 mm
250 mm x 275 mm
1
Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc
Stainless steel 1.4301 (AISI 304)
1 pc(s).
6.321
6.335
94032080
4028177815063
E3465120
EC000261
EC000261
27180101

© Rittal 2025 3

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 4