Rittal – The System.

Faster – better – everywhere.





AE 1005.600 Wall-mounted AE

State: 2025-11-18 (Source: rittal.com/ca-en)



AE 1005.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1005.600
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s) Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 300 mm Height: 380 mm Depth: 210 mm
Dimensions of mounting plate (W x H)	275 mm x 334 mm
Number of doors	1
No. of locks	1
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated
Base material	Stainless steel 1.4301 (AISI 304)

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	7.7
Gross weight	7.88
Customs tariff number	94032080
EAN	4028177000148
E-Number Sweden	E3404406
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3