


Rittal – The System.

Faster – better – everywhere.



AX 1006.000

Basic enclosure AX, stainless steel

State: 2025-08-28 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1006.000 - Basic enclosure AX, stainless steel

The robust stainless steel housings feature an integrated cam system that allows for extensive system expansion without drilling, quickly and securely.



Features

Model No.	AX 1006.000
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing with door(s), swing angle 130° Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60529	IP 66

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
IK code	IK10
Dimensions	Width: 380 mm Height: 380 mm Depth: 210 mm
Material thickness - door	1.5 mm
Material thickness - enclosure	1.25 mm
Material thickness – mounting plate	2 mm
Dimensions of mounting plate (W x H)	330 mm x 355 mm
Number of doors	1
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	9
Gross weight	9.115
Customs tariff number	94032080
EAN	4028177814950
E-Number Sweden	E3465122
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Declaration of conformity
Declaration of conformity UK