

Rittal – The System.

Faster – better – everywhere.



AE 1013.600

Compact enclosures AE

State: 2024-04-30 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1013.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

Features

Model No.	AE 1013.600
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Housing with door(s) Mounting plate Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 500 mm Height: 500 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	449 mm x 470 mm
Number of doors	1
No. of locks	2
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated
Base material	Stainless steel 1.4301 (AISI 304)

Features

Packaging unit	1 pc(s).
Weight/packaging unit	18.4 kg
Customs tariff number	94032080
EAN	4028177244306
E-Number Sweden	E3404420
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK