

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.915 Connection block

State: 29.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.915 - Connection block

For connecting cables and laminated copper bars.

## Features

Model No.	SV 9677.915
Product description	For connecting cables and laminated copper bars.
Material	Sheet steel, zinc-plated E-Cu, tin-plated
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
Rated current max.	1000 A
Dimensions	Width: 98 mm
Connection of round conductors	185 - 300 mm <sup>2</sup>
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Net weight	1,2 kg
Gross weight	1,35 kg
Copper weight (kg per piece)	0,893
PCF per pack (cradle-to-gate)	5.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection block, 1000 A, 690 V, 1-pole, cable outlet top/bottom, round conductor connection 185-300 mm <sup>2</sup>

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---