Rittal – The System.

Faster – better – everywhere.



AX 1011.000

Basic enclosure AX, stainless steel

State: 2026-11-13 (Source: www.rittal.com/ca-en)

AX 1011.000 - Basic enclosure AX, stainless steel

The robust stainless steel housings feature an integrated cam system that allows for extensive system expansion without drilling, quickly and securely.







Features

Model No.	AX 1011.000
Material	Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain size 400 Mounting panel: Zinc-plated
Supply includes	Housing with door(s), swing angle 130° Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60 529	IP 66
Type rating according to 508A	Type 1 Type 3R Type 4 Type 4X Type 12

© Rittal 2026

Features

IK code	IK10
Dimensions	Width: 380 mm Height: 300 mm Depth: 210 mm
Material thickness - door	1.5 mm
Material thickness - enclosure	1.25 mm
Material thickness – mounting plate	2 mm
Dimensions of mounting plate (W x H)	330 mm x 275 mm
Number of doors	1
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit Material lock: Die-cast zinc
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	7.1 kg
Gross weight	7.532 kg
PCF/VE (cradle-to-gate)	29.35
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AX wall-mounted enclosure, WHD: 380x300x210 mm, 304 stainless steel, with mounting panel, single-door, with one cam locks

Approvals

Approvals

Approvals	Bureau Veritas DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration