Rittal – The System.

Faster – better – everywhere.





AE 1012.600 Wall-mounted AE

State: 2025-11-17 (Source: rittal.com/ca-en)



AE 1012.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

Model No.	AE 1012.600
Material	Housing: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Carbon steel
	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height
	< 0.8 µm
	Mounting panel: Zinc-plated
Supply includes	Housing with door(s)
	Mounting panel
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 600 mm
	Height: 760 mm
	Depth: 210 mm
Dimensions of mounting plate (W x H)	549 mm x 730 mm
Number of doors	1
No. of locks	2
Lock	Lock version: Cam
	No. of locks: 2
	Lock Insert: 3 mm double-bit
	Material lock: Die-cast zinc, nickel-plated

© Rittal 2025

Features

Packaging unit	1 pc(s).
Net weight	28.5
Gross weight	30
Customs tariff number	94032080
EAN	4028177000476
E-Number Sweden	E3404418
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3