Rittal – The System.

Faster – better – everywhere.





AE 1014.600 Wall-mounted AE

State: 2025-11-29 (Source: rittal.com/ca-en)



AE 1014.600 - Wall-mounted AE Stainless steel

Wall-mounted enclosure AE in stainless steel including mounting panel

Features

| Model No. | AE 1014.600 |
|--|---|
| Material | Housing: Stainless steel |
| | Door: Stainless steel, all-round foamed-in PU seal |
| | Mounting plate: Carbon steel |
| | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Housing and door: Brushed, grain 400, peak-to-valley height |
| | < 0.8 µm |
| | Mounting panel: Zinc-plated |
| Supply includes | Housing with door(s) |
| | Mounting panel |
| | Lock: 3 mm double-bit |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60 529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 760 mm |
| | Height: 760 mm |
| | Depth: 300 mm |
| Dimensions of mounting plate (W x H) | 704 mm x 730 mm |
| Number of doors | 1 |
| No. of locks | 2 |
| Lock | Lock version: Cam |
| | No. of locks: 2 |
| | Lock Insert: 3 mm double-bit |
| | Material lock: Die-cast zinc, nickel-plated |
| | |

© Rittal 2025

Features

| Packaging unit | 1 pc(s). |
|-----------------------|---------------|
| Net weight | 40.4 |
| Gross weight | 42.5 |
| Customs tariff number | 94032080 |
| EAN | 4028177000520 |
| E-Number Sweden | E3404422 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| Approvals | DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |

© Rittal 2025 3