

# Rittal – The System.

Faster – better – everywhere.



## AE 1032.500

### Wall-mounted AE

State: 2026-02-19 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1032.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

## Features

Model No.	AE 1032.500
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 12
Protection category IP to EN 60 529	IP 55
IK code	IK08
Dimensions	Width: 200 mm Height: 300 mm Depth: 120 mm
Material thickness - door	1.5 mm
Material thickness - enclosure	1.25 mm
Material thickness – mounting plate	2 mm
Dimensions of mounting plate (W x H)	162 mm x 275 mm
Number of doors	1
No. of locks	1

## Features

---

Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit
Gland plate	Size: 1 Qty.: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.9 kg
Gross weight	4 kg
Customs tariff number	94032080
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 200x300x120 mm, Sheet steel, with mounting plate, single-door, with one cam lock

---

## Approvals

---

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---