

# Rittal – The System.

Faster – better – everywhere.



## HD 1317.600

# Compact enclosure HD, single-door

State: 2026-06-29 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 1317.600 - Compact enclosure HD, single-door

Enclosure solution tailored to the requirements of the food and beverage industry. Roof angled forwards by 30°. Seal dyed blue to clearly distinguish it from foodstuffs



## Features

|                 |                                                                                                                                                                                                            |
|-----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.       | HD 1317.600                                                                                                                                                                                                |
| Version         | Hygienic Design Enclosures                                                                                                                                                                                 |
| Product changes | From June 2020, the compact enclosure HD, single-door, comes with the new compact enclosure AX mounting plate.                                                                                             |
| Material        | Housing and door: Stainless steel 1.4301 (AISI 304)<br>Mounting plate: Carbon steel<br>HD lock inserts: Stainless steel 1.4404 (AISI 316L)<br>Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 |
| Surface finish  | Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm<br>Mounting panel: Zinc-plated<br>Seal: Blue, dyed (RAL 5010)                                                                         |
| Supply includes | Housing of all-round solid construction<br>Door with fitted seal<br>Door hinged on the right, may be swapped to the left<br>Mounting panel                                                                 |
| Dimensions      | Width: 810 mm<br>Height, front: 1,250 mm<br>Height rear: 1,421 mm<br>Depth: 300 mm                                                                                                                         |

# Features

|                                      |                                                                                                                                          |
|--------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensions of mounting plate (W x H) | 745 mm x 1,175 mm                                                                                                                        |
| Door opening angle                   | 125°                                                                                                                                     |
| No. of locks                         | 2                                                                                                                                        |
| IK code                              | IK08                                                                                                                                     |
| Base material                        | Stainless steel 1.4301 (AISI 304)                                                                                                        |
| Protection category IP to IEC 60529  | IP 66<br>IP X9                                                                                                                           |
| Protection category NEMA             | NEMA 1<br>NEMA 3<br>NEMA 3X<br>NEMA 4<br>NEMA 4X<br>NEMA 12<br>NEMA 13                                                                   |
| Type rating according to UL 50E      | Type 1<br>Type 3<br>Type 3X<br>Type 4<br>Type 4X<br>Type 12<br>Type 13                                                                   |
| Packaging unit                       | 1 pc(s).                                                                                                                                 |
| Net weight                           | 68.87 kg                                                                                                                                 |
| Gross weight                         | 71 kg                                                                                                                                    |
| PCF/VE (cradle-to-gate)              | 216.61                                                                                                                                   |
| Customs tariff number                | 94032080                                                                                                                                 |
| ETIM 9                               | EC000261                                                                                                                                 |
| ETIM 8                               | EC000261                                                                                                                                 |
| ECLASS 8.0                           | 27180101                                                                                                                                 |
| Product description                  | HD Compact enclosure, WHD: 810x1250(H1)x1421(H2)x300 mm, Stainless steel 1.4301, with mounting plate, with hinged door and silicone seal |

# Approvals

---

Approvals

UL + C-UL (listed)

---

Explanations

Declaration of conformity

Declaration of conformity UK

PCF-declaration