

# Rittal – The System.

Faster – better – everywhere.



## AE 1038.500 Wall-mounted AE

State: 2025-06-23 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1038.500 - Wall-mounted AE

Housing with door of carbon steel, spray-finished with mounting plate and gland panel in the base.

## Features

Model No.	AE 1038.500
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting panel Lock: 3 mm double-bit
Protection category NEMA	NEMA 4
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 380 mm Height: 600 mm Depth: 210 mm
Material thickness - door	1.5 mm
Material thickness - enclosure	1.38 mm
Material thickness – mounting plate	2.5 mm
Dimensions of mounting plate (W x H)	334 mm x 570 mm
Number of doors	1
Interchangeable door catch	Yes

## Features

No. of locks	2
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Gland plate	Size: 3 Qty.: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	14.008
Gross weight	14.9
Customs tariff number	94032080
EAN	4028177252035
E-Number Sweden	E3404608
ECLASS 8.0	27180101

## Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK