## Rittal - The System.

Faster – better – everywhere.





# AX 1095.000 Basic enclosure AX, carbon steel

State: 2025-11-01 (Source: rittal.com/ca-en)




### AX 1095.000 - Basic enclosure AX, carbon steel

The AX wall-mounted enclosure with embossed enclosure cams in the roof, base and side replicates the familiar 25 mm system grid from the VX25 large enclosure. Thanks to this unique, patented system, AX wall-mounted control enclosures are prepared for all expansion and retrofit cases. System components and accessories can be installed and retrofitted easily, quickly and safely on rails without drilling.







#### **Features**

Model No.	AX 1095.000	
Benefits	More interior finishing options thanks to integrated housing cams in the 25 mm system grid in combination with the rail for interior	
	finishing and our wide range of system accessories	
	Maintaining the protection class (UL approval) by mounting the rail	
	for interior installation without drilling	
	Additional mounting level and increased load capacity due to base	
	configuration rail	
	Easy planning and configuration with the Rittal configurator RiPanel	
Material	Housing: Carbon steel	
	Door: Carbon steel, all-round foamed-in PU seal	
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,	
	textured paint	
	Mounting panel: Zinc-plated	
Color	RAL 7035	

© Rittal 2025 2

## **Features**

Supply includes	Housing with door(s) Flange (gland) plate(s) in enclosure base Mounting panel Punched door strip Lock: 3 mm double-bit
Protection category IP to EN 60 529	IP 55
Type rating according to UL 50E	Type 1 Type 12
IK code	IK10
Dimensions	Width: 800 mm Height: 400 mm Depth: 300 mm
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness – mounting plate	2 mm
Dimensions of mounting plate (W x H)	750 mm x 375 mm
Number of doors	2
No. of locks	2
Lock	Lock version: Cam Lock Insert: 3 mm double-bit
Gland plate	Size: 5 Qty.: 2
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	24.577
Gross weight	24.889
Customs tariff number	94032080
EAN	4028177995246

© Rittal 2025 3

## **Features**

ETIM 9	EC000261	
ETIM 8	EC000261	
ECLASS 8.0	27180101	

## **Approvals**

Approvals	UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration  Declaration of conformity
	Declaration of conformity UK

© Rittal 2025