## Rittal – The System.

Faster – better – everywhere.





# KL 1529.010 KL Terminal Boxes

State: 2025-10-28 (Source: rittal.com/ca-en)



## KL 1529.010 - KL Terminal Boxes Stainless steel

Terminal box of stainless steel 1.4301, (AISI 304). Protection category IP 66.

#### **Features**

| Model No.                              | KL 1529.010  |
|--|--|
| Material                               | Housing: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea |
| Surface finish                         | Housing and cover: Brushed, grain 180  |
| Supply includes                        | Housing with cover Quick-release fasteners including plastic bushings  |
| Protection category NEMA               | NEMA 4X  |
| Protection category IP to EN 60<br>529 | IP 66  |
| IK code                                | IK08   |
| Dimensions                             | Width: 300 mm<br>Height: 200 mm<br>Depth: 120 mm   |
| Material thickness - cover             | 1.25 mm  |
| Material thickness - enclosure         | 1.25 mm  |
| Lock                                   | No. of locks: 4  |
| Base material                          | Stainless steel 1.4301 (AISI 304)  |
| Packaging unit                         | 1 pc(s).   |
| Net weight                             | 2.7  |
| Gross weight                           | 2.975  |
| Customs tariff number                  | 84879090   |
| EAN                                    | 4028177663343  |
| E-Number Sweden                        | E3404380   |
| ETIM 9                                 | EC000261   |
|  |  |

© Rittal 2025

## **Features**

| ETIM 8     | EC000261 |
|------------|----------|
| ECLASS 8.0 | 27180101 |

# **Approvals**

| Approvals    | Bureau Veritas               |
|--------------|------------------------------|
|              | DNV-GL                       |
|              | UL + C-UL (listed)           |
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |

© Rittal 2025 3