Rittal - The System.

Faster – better – everywhere.





KX 1532.000

KX terminal box, carbon steel with flange

State: 2025-11-06 (Source: rittal.com/ca-en)



KX 1532.000 - KX terminal box, carbon steel with flange

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.







Features

KX 1532.000
Housing: Carbon steel
Cover: Carbon steel, all-round foamed-in PU seal
Housing and cover: Dipcoat primed, powder-coated on the outside,
textured paint
RAL 7035
Housing with cover
Mini-fasteners
Carbon steel flange plates with seals and assembly components
NEMA 1
NEMA 12
IP 55
Type 1
Type 12
IK08

© Rittal 2025 2

Features

Dimensions	Width: 400 mm
	Height: 200 mm
	Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Flange Plates	:1+1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.723
Gross weight	3.823
PCF/VE (cradle-to-gate)	16.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816381
E-Number Sweden	E3465204
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity Declaration of conformity UK PCF-declaration

© Rittal 2025