Rittal – The System.

Faster – better – everywhere.





KX 1547.000 E-box KX, carbon steel

State: 2025-11-06 (Source: rittal.com/ca-en)



KX 1547.000 - E-box KX, carbon steel

The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.







Features

Model No.	KX 1547.000
Product description	The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door Mounting panel Cam lock with 3 mm double-bit insert 180° hinge
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Protection category IP to EN 60 529	IP 66

© Rittal 2025

Features

Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
IK code	IK08
Dimensions	Width: 200 mm Height: 400 mm Depth: 80 mm
Dimensions of mounting plate (W x H)	175 mm x 385 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Material thickness – mounting plate	2 mm
Lock	No. of locks: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	3.848
Gross weight	4.153
PCF/VE (cradle-to-gate)	13.7 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816497
E-Number Sweden	E3465215
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

© Rittal 2025 3

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

© Rittal 2025