Rittal – The System.

Faster – better – everywhere.





KX 1566.000 KX terminal box

State: 2025-11-06 (Source: rittal.com/ca-en)



KX 1566.000 - KX terminal box Stainless steel

The KX small enclosure stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.







Features

Model No.	KX 1566.000
Product description	System perfection. The new small enclosure KX, stainless steel offers maximum data quality and consistency in engineering, flexibility, and safety for a variety of applications.
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 180
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 1 NEMA 3R NEMA 3RX NEMA 4 NEMA 4X NEMA 12
Protection category IP to EN 60 529	IP 66

© Rittal 2025

Features

Type rating according to UL 50E	Type 1
	Type 3R
	Type 3RX
	Type 4
	Type 4X
	Type 12
Dimensions	Width: 300 mm
	Height: 200 mm
	Depth: 120 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Lock	No. of locks: 4
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	2.7
Gross weight	2.866
Customs tariff number	84879059
EAN	4028177919204
E-Number Sweden	E3465232
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3