Rittal - The System.

Faster – better – everywhere.





KX 1611.000

KX bus housing, carbon steel, with mini cam lock

State: 2025-11-04 (Source: rittal.com/ca-en)



KX 1611.000 - KX bus housing, carbon steel, with mini cam lock

Wall-mounted enclosure made of carbon steel, with cover and viewing window. Protection category IP 65/NEMA 12. For installation of most brands of bus modules and sensors.







Features

Model No.	KX 1611.000
Version	with viewing window
Material	Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal Viewing window: Polycarbonate, 4 mm1
Surface finish	Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing with hinged cover Sight glass in cover Mini-fasteners
Protection category NEMA	NEMA 1 NEMA 12
Protection category IP to EN 60 529	IP 65
Type rating according to UL 50E	Type 1 Type 12

© Rittal 2025

Features

IK code	IK08
Dimensions	Width: 400 mm
	Height: 300 mm
	Depth: 155 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	4.78
Gross weight	5
PCF/VE (cradle-to-gate)	24.8 kg CO2 eq (Cat B)
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on
class	the basis of the product weight and self-declared
Customs tariff number	84879059
EAN	4028177816688
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Bureau Veritas
C-UL
DNV-GL
Lloyds Register of Shipping
Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK
PCF-declaration

© Rittal 2025 3