


Rittal – The System.

Faster – better – everywhere.



SZ 2370.500

LED flashing light component

State: 2025-11-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2370.500 - LED flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, no. of potential stages = 5 components, with identical voltage.

Features

Model No.	SZ 2370.500
Version	LED flashing light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Red
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Dimensions	Height: 56 mm
Protection category IP to EN 60529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.082

Features

Gross weight	0.083
Customs tariff number	94054990
EAN	4028177659216
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------