Rittal – The System.

Faster - better - everywhere.





EB 1546.500 E-Box EB

State: 2025-11-16 (Source: rittal.com/ca-en)



EB 1546.500 - E-Box EB

Wall-mounted housing with door and mounting plate made from sheet steel. Protection category IP 66. With 180° hinge. Lock insert may be exchanged for individual lock systems.

Features

Model No.	EB 1546.500
Material	Housing and door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door 180° hinge Cam lock with 3 mm double-bit insert Mounting panel
Protection category NEMA	NEMA 4
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 200 mm Height: 200 mm Depth: 80 mm
Dimensions of mounting plate (W x H)	175 mm x 185 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Material thickness – mounting plate	2 mm
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit

© Rittal 2025

Features

Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	2.16
Gross weight	2.28
Customs tariff number	94032080
EAN	4028177251717
E-Number Sweden	E3404641
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	C-UL
	Lloyds Register of Shipping
	UL
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3