


Rittal – The System.

Faster – better – everywhere.



SG 2372.010

LED steady light component

State: 2025-05-13 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.010 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimized prism system, number of potential stages = 5 components, with identical voltage.

Features

Model No.	SG 2372.010
Version	LED steady light component
Product description	With 360° signal transmission thanks to optimized prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Easy mounting and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colors and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel.
Material	Housing of polyamide Cap: Transparent polycarbonate
Color	Green
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC
Rated current max.	25 mA
Dimensions	Height: 56 mm
Protection category IP to EN 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)
Packaging unit	1 pc(s).
Net weight	0.08

Features

Gross weight	0.088
Customs tariff number	85311095
EAN	4028177220188
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220

Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------