## Rittal – The System.

Faster - better - everywhere.







## SG 2372.101 - Signal pillar 3-fold LED

Rittal offers a flexible range of signal pillars for every application to instantaneously detect faults and operating states in machines and automated processes. The ready-to-connect three-way LED signal system is ideal if three standard signal colors are sufficient.

## **Features**

Version for conduit mounting  Benefits Complete, ready-to-connect solution Extremely long service life of the LEDs (up to 100,000 hou therefore maintenance-free) Minimal assembly work and warehousing costs  Technical specifications 3-stage, red, yellow, green Angle of projection: 3 x 120°  Cable entry Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm  Type of connection (electrical) Clamp terminals  Light (bulb) LEDs  Dimensions Height: 211.5 mm  Operating temperature range -20 °C50 °C  Protection category IP to EN 60 IP 65  529  Rated operating voltage 24 V  Thread M12 x 1.5	S,
Extremely long service life of the LEDs (up to 100,000 hou therefore maintenance-free) Minimal assembly work and warehousing costs  Technical specifications  3-stage, red, yellow, green Angle of projection: 3 x 120°  Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm  Type of connection (electrical)  Clamp terminals  Light (bulb)  LEDs  Dimensions  Height: 211.5 mm  Operating temperature range  -20 °C50 °C  Protection category IP to EN 60 529  Rated operating voltage  24 V  Thread  M12 x 1.5	S,
Angle of projection: 3 x 120°  Cable entry  Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm  Type of connection (electrical)  Clamp terminals  Light (bulb)  LEDs  Dimensions  Height: 211.5 mm  Operating temperature range  -20 °C50 °C  Protection category IP to EN 60 529  Rated operating voltage  24 V  Thread  M12 x 1.5	
Max. cable diameter: 6.5 mm  Type of connection (electrical)  Light (bulb)  LEDs  Dimensions  Height: 211.5 mm  Operating temperature range  -20 °C50 °C  Protection category IP to EN 60 529  Rated operating voltage  24 V  Thread  M12 x 1.5	
Light (bulb)  LEDs  Dimensions  Height: 211.5 mm  Operating temperature range  -20 °C50 °C  Protection category IP to EN 60 529  Rated operating voltage  24 V  Thread  M12 x 1.5	
Dimensions Height: 211.5 mm  Operating temperature range -20 °C50 °C  Protection category IP to EN 60 IP 65 529  Rated operating voltage 24 V  Thread M12 x 1.5	
Operating temperature range -20 °C50 °C  Protection category IP to EN 60 IP 65  529  Rated operating voltage 24 V  Thread M12 x 1.5	
Protection category IP to EN 60 IP 65 529  Rated operating voltage 24 V  Thread M12 x 1.5	
529 Rated operating voltage 24 V Thread M12 x 1.5	
Thread M12 x 1.5	
Packaging unit 1 pc(s).	
Net weight 0.25	
Gross weight 0.308	
Customs tariff number 85318070	
EAN 4028177953758	

© Rittal 2025 2

## **Features**

ETIM 9	EC001042	
ETIM 8	EC001042	
ECLASS 8.0	27371230	

© Rittal 2025 3