

# Rittal – The System.

Faster – better – everywhere.



## SM 2384.010 Pushbutton Housings

State: 2026-03-23 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 2384.010 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

## Features

Model No.	SM 2384.010
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 100 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Hole pattern	60 mm
Breakouts (number x Ø)	1 x 22.5 mm
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 2
Cable entry (quantity x diameter)	1
No. of metric knockouts	1
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	0.68 kg

# Features

---

Gross weight	0.72 kg
Customs tariff number	94039910
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	SM Switch housing, WHD: 100x100x90 mm, Stainless steel 1.4301, without mounting plate, 1 switch cut-out

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---