

Rittal – The System.

Faster – better – everywhere.



SM 2384.030 Pushbutton Housings

State: 2026-07-10 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.030 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

Features

Model No.	SM 2384.030
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60529	IP 66
IK code	IK08
Dimensions	Width: 220 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Hole pattern	60 mm
Breakouts (number x Ø)	3 x 22.5 mm
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 4
Cable entry (quantity x diameter)	3
No. of metric knockouts	3
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	1.1 kg

Features

Gross weight	1.226 kg
PCF/VE (cradle-to-gate)	4.46
Customs tariff number	84879090
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	SM Switch housing, WHD: 220x100x90 mm, Stainless steel 1.4301, without mounting plate, 3 switch cut-outs

Approvals

Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration
--------------	--