

Rittal – The System.

Faster – better – everywhere.



KX 1574.000

KX small housing

State: 2024-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1574.000 - KX small housing E-box KX, carbon steel

The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.

Features

Model No.	KX 1574.000
Product description	The small enclosure KX, E-Box KX, carbon steel offers remarkable ease of assembly and flexibility when selecting lock systems.
Material	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door Mounting plate Cam lock with 3 mm double-bit insert 180° hinge
Protection category NEMA	NEMA 1, 3R, 4, 12
Protection category IP to EN 60 529	IP 66
Type rating according to UL 50E	Type 1, 3R, 4, 12
IK code	IK08
Dimensions	Width: 200 mm Height: 300 mm Depth: 155 mm
Dimensions of mounting plate (W x H)	175 mm x 285 mm
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm

Features

Material thickness – mounting plate	2 mm
Lock	No. of locks: 1
Base material	Carbon steel
Packaging unit	1 pc(s).
Weight/packaging unit	3.98 kg
Customs tariff number	94032080
EAN	4028177816602
E-Number Sweden	E3465236
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Protection category
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK