

# Rittal – The System.

Faster – better – everywhere.




## HD 2410.001

## Cable gland HD

State: 2026-01-11 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))

# HD 2410.001 - Cable gland HD

The design is more compact and the locknut is already included.



## Features

Model No.	HD 2410.001
Version	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Production and packaging of food and beverages Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Incl. lock nut
Dimensions	Thread: M12 x 1.5
For cable diameters	3 - 6.5 mm
Operating temperature range	-20 °C...100 °C

## Features

---

Protection category IP to IEC 60  
529 IP69 / IPX8 (5 bar, 30 min)

---

Packaging unit 5 pc(s).

---

Net weight 0.095

---

Gross weight 0.134

---

Customs tariff number 73072980

---

EAN 4028177928640

---

ETIM 9 EC000441

---

ETIM 8 EC000441

---

ECLASS 8.0 27149109

---

## Approvals

---

Approvals UR + C-UR (recognized)  
VDE