


Rittal – The System.

Faster – better – everywhere.



HD 2410.011 Cable gland HD

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

HD 2410.011 - Cable gland HD

The design is more compact and the locknut is already included.



Features

Model No.	HD 2410.011
Version	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Production and packaging of food and beverages Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Incl. lock nut
Dimensions	Thread: M16 x 1.5
For cable diameters	5 - 10 mm
Operating temperature range	-20 °C...100 °C

Features

Protection category IP to IEC 60
529 IP69 / IPX8 (5 bar, 30 min)

Packaging unit 5 pc(s).

Net weight 0.1

Gross weight 0.2

Customs tariff number 73072980

EAN 4028177928718

ETIM 9 EC000441

ETIM 8 EC000441

ECLASS 8.0 27149109

Approvals

Approvals UR + C-UR (recognized)
VDE