

# Rittal – The System.

Faster – better – everywhere.



## HD 2410.021

## Cable gland HD

State: 2026-02-06 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# HD 2410.021 - Cable gland HD

The design is more compact and the locknut is already included.



## Features

Model No.	HD 2410.021
Version	Standard
Benefits	Smooth, solid exterior surfaces effectively prevent the accumulation of harmful micro-organisms. Much easier, and therefore cheaper to clean compared with conventional cable glands.
Applications	Production and packaging of food and beverages Clean room technology (e.g. pharmaceuticals) Biotechnology Chemical industry
Material	Nut: Stainless steel 1.4305 (AISI 303) Seal: EPDM, compliant with FDA 21 CFR 177.2600
Supply includes	Incl. lock nut
Dimensions	Thread: M20 x 1.5
For cable diameters	6 - 12 mm
Operating temperature range	-20 °C...100 °C

# Features

---

Protection category IP to IEC 60529	IP69 / IPX8 (5 bar, 30 min)
Type rating according to UL 50E	Type 1 Type 2 Type 4 Type 4X Type 12 Type 12K Type 13
Packaging unit	5 pc(s).
Net weight	0.33
Gross weight	0.333
Customs tariff number	73072980
EAN	4028177928701
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

---

# Approvals

---

Approvals	UL + C-UL (listed) VDE
-----------	---------------------------

---