

Rittal – The System.

Faster – better – everywhere.



KX 1588.000

E-box KX

State: 2026-04-06 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1588.000 - E-box KX Stainless steel

The E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior.



Features

| | |
|------------------------------------|---|
| Model No. | KX 1588.000 |
| Product description | The small enclosure KX, E-Box KX, stainless steel offers remarkable ease of assembly and flexibility when selecting lock systems. The standard 180° hinges provide easy access to the enclosure interior. |
| Material | Housing: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Carbon steel Stainless steel 1.4301 (AISI 304) |
| Surface finish | Housing and cover: Brushed, grain 180 Mounting panel: Zinc-plated |
| Supply includes | Mounting panel Cam lock with 3 mm double-bit insert |
| Protection category IP to EN 60529 | IP 65 |
| Type rating according to UL 50E | Type 1 Type 3R Type 3RX Type 4 Type 4X Type 12 |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 380 mm Height: 300 mm Depth: 155 mm |
| Dimensions of mounting plate (W x H) | 365 mm x 275 mm |
| Material thickness - enclosure | 1.25 mm |
| Material thickness - door | 1.25 mm |
| Lock | No. of locks: 1 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 6.4 kg |
| Gross weight | 6.5 kg |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX E-Box, WHD: 380x300x155 mm, stainless steel 1.4301, with mounting plate, single-door, with cam lock |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity |
