

Rittal – The System.

Faster – better – everywhere.



KX 1611.100

Bus housing KX, carbon steel, with double-bit insert

State: 2026-05-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KX 1611.100 - Bus housing KX, carbon steel, with double-bit insert

Wall-mounted enclosure made of carbon steel, with cover and viewing window. Protection category IP 65/NEMA 12. For installation of most brands of bus modules and sensors.



Features

| | |
|------------------------------------|--|
| Model No. | KX 1611.100 |
| Version | with viewing window |
| Material | Housing: Carbon steel Cover: Carbon steel, all-round foamed-in PU seal Viewing window: Polycarbonate, 4 mm1 Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Color | RAL 7035 |
| Supply includes | Housing with hinged cover Sight glass in cover Mounting panel Cam lock with 3 mm double-bit insert |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Protection category IP to EN 60529 | IP 65 |

Features

| | |
|-------------------------------------|--|
| Type rating according to UL 50E | Type 1 Type 12 |
| IK code | IK08 |
| Dimensions | Width: 400 mm Height: 300 mm Depth: 155 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Material thickness – mounting plate | 2 mm |
| Base material | Carbon steel |
| Customs tariff number | 84879059 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | KX bus housing, WHD: 400x300x155 mm, with mounting plate, with cam |

Approvals

| | |
|-----------|------|
| Approvals | C-UL |
|-----------|------|