


Rittal – The System.

Faster – better – everywhere.



SZ 2411.661

Cable gland, polyamide

State: 2025-07-12 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.661 - Cable gland, polyamide

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.661
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Polyamide 6 Seal: CR/NBR
Color	RAL 7035
Protection category IP to IEC 60529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 53.5 mm
Thread	M50 x 1.5
Thread length	18 mm
Min. cable diameter	30 mm
Max. cable diameter	38 mm
Operating temperature range	-30 °C...100 °C
torque	12 Nm
Width across flats	60 mm
Dimensions	Thread: M50 x 1.5 Thread length: 18 mm
Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packaging unit	5 pc(s).

Features

Net weight	0.535
Gross weight	0.541
Customs tariff number	39269097
EAN	4028177809949
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK