

Rittal – The System.

Faster – better – everywhere.



SZ 2411.811

Cable gland, brass

State: 2026-01-14 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2411.811 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.811
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Protection category IP to IEC 60 529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 28 mm
Thread	M16 x 1.5
Thread length	7 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-40 °C...100 °C
torque	9 Nm
Width across flats	20 mm
Dimensions	Thread: M16 x 1.5 Thread length: 7 mm
Type rating according to UL 50E	Type 4X
Packaging unit	15 pc(s).
Net weight	0.3
Gross weight	0.451

Features

Customs tariff number 74198090

EAN 4028177810082

ETIM 9 EC000441

ETIM 8 EC000441

ECLASS 8.0 27149109

Approvals

Approvals UR + C-UR (recognized)
VDE

Explanations Declaration of conformity
Declaration of conformity UK