

Rittal – The System.

Faster – better – everywhere.



AX 2262.155

AX wall-mounted housing, 3-part

State: 2026-02-28 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2262.155 - AX wall-mounted housing, 3-part with Blue e+ outlet filter

The delivery concept of the three-part AX wall-mounted enclosures reduces complexity and increases flexibility. Thanks to the AX/VX modular system, the enclosures are suitable for various applications. The three-part structure ensures easy access.



Features

| | |
|-----------------|--|
| Model No. | AX 2262.155 |
| Version | Wall-mounted housing IT |
| Material | Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray) |
| Supply includes | Wall section: Flange (gland) plate, solid, top and bottom Hinged part with 25 mm pitch pattern in the front and rear frame, two 19" profile angles at the front, fixed in place Designer viewing door Lock design – glazed door: Security lock 3524 E Center part lock: 3 mm double bit 2 Blue e+ outlet filters 3238.300 (enclosed loose) Comfort handle for lock inserts and 2-point locking |
| Height units | 21 U |

Features

| | |
|---------------------------------------|---|
| Dimensions | Width: 600 mm Height: 1,012 mm Depth: 573 mm |
| Installation depth | 520 mm |
| Clearances | Clearance width: 502 mm Clearance height: 951 mm |
| Depth hinged part | 416 mm |
| Depth of wall section | 135 mm |
| No. of locks | 1 |
| IK code | IK08 |
| Load capacity of hinged part (static) | 750 N |
| Load capacity wall section (static) | 250 N |
| Base material | Carbon steel |
| Lock | Lock version: Comfort handle and 2-point locking Lock Insert: Security lock insert no. 3524 E |
| Protection category IP to EN 60 529 | IP 54 in conjunction with solid gland plate top and bottom |
| Customs tariff number | 94032080 |
| Product description | AX wall-mounted enclosure, 3-part, W x H x D: 600 x 1012 x 573 mm, 21 U, wall part: closed flange plate top and bottom, with comfort handle |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|