## Rittal – The System.

Faster – better – everywhere.





# SZ 2411.861 Cable gland, brass

State: 2025-11-16 (Source: rittal.com/ca-en)



## SZ 2411.861 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

#### **Features**

Model No.	SZ 2411.861
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.  Clamping membranes for even tightening and strain relief that protects the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Protection category IP to IEC 60 529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 52 mm
Thread	M50 x 1.5
Thread length	9 mm
Min. cable diameter	27 mm
Max. cable diameter	38 mm
Operating temperature range	-40 °C100 °C
torque	35 Nm
Width across flats	58 mm
Dimensions	Thread: M50 x 1.5 Thread length: 9 mm
Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packaging unit	2 pc(s).

© Rittal 2025

### Features

Net weight	0.6
Gross weight	0.678
Customs tariff number	74198090
EAN	4028177810037
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

## **Approvals**

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3