## Rittal – The System.

Faster – better – everywhere.





# SZ 2500.110 LED system light

State: 2025-11-17 (Source: rittal.com/ca-en)



## SZ 2500.110 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.





#### **Features**

Model No.	SZ 2500.110
Version	without socket
Benefits	Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application
Version	without socket
Material	Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	Assembly screws
Rated power	7 W
Connection options	Power Supply, 2-pole Through-wiring, 2-pole Door-operated switch
Protection category	II (total insulation)

© Rittal 2025

### Features

Light – installation type	Screw fastening
	Clip fastening
	Magnetic fastener (accessories)
Installation options	The internal mounting rail AX and the mounting bracket are required
	when installing in compact enclosures
	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	600 lm
Light color	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 337 mm
	Height: 55 mm
	Depth: 23 mm
Operating temperature range	-20 °C55 °C
Rated operating voltage	100 V - 230 V, 1~, 50 Hz/60 Hz
Protection category IP to IEC 60 529	IP 20
Packaging unit	1 pc(s).
Net weight	0.263
Gross weight	0.351
Customs tariff number	94054990
EAN	4028177806948
E-Number Sweden	E3465306
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

# Approvals

Approvals ENEC	Approvals
----------------	-----------

# **Approvals**

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025