

Rittal – The System.

Faster – better – everywhere.



SG 2372.102

Signal pillar 3-fold LED

State: 2026-04-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.102 - Signal pillar 3-fold LED

Rittal offers a flexible range of signal pillars for every application to instantaneously detect faults and operating states in machines and automated processes. The ready-to-connect three-way LED signal system is ideal if three standard signal colors are sufficient.

Features

Model No.	SG 2372.102
Version	for wall/base mounting
Benefits	Complete, ready-to-connect solution Extremely long service life of the LEDs (up to 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs
Technical specifications	3-stage, red, yellow, green Angle of projection: 3 x 120°
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Type of connection (electrical)	Clamp terminals
Light (bulb)	LEDs
Dimensions	Height: 211.5 mm
Operating temperature range	-20 °C...50 °C
Protection category IP to EN 60529	IP 65
Rated operating voltage	24 V
Thread	M12 x 1.5
Note	The signal pillar is comprised of items 2372001, 2372021, 2372011 and 2368002
Packaging unit	1 pc(s).
Net weight	0.25 kg
Gross weight	0.309 kg

Features

Customs tariff number	85318070
ETIM 9	EC001042
ETIM 8	EC001042
ECLASS 8.0	27371230
Product description	SG signal pillar, LED compact for wall mounting

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------
