Rittal – The System.

Faster – better – everywhere.





SM 2384.020 Pushbutton Housings

State: 2025-11-18 (Source: rittal.com/ca-en)



SM 2384.020 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with \emptyset 22.5 mm switch cut-outs. Protection category IP 66.

Features

Model No.	SM 2384.020
Material	Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU sea
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Housing with cover Quick-release fasteners including plastic bushings
Protection category NEMA	NEMA 4X
Protection category IP to EN 60 529	IP 66
IK code	IK08
Dimensions	Width: 160 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Hole pattern	60 mm
Breakouts (number x Ø)	2 x 22.5 mm
Lock	Lock version: Quick-release fasteners including plastic bushings No. of locks: 4
Cable entry (quantity x diameter)	2
No. of metric knockouts	2
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).

© Rittal 2025

Features

Gross weight	1
Customs tariff number	94039910
EAN	4028177529410
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3