

Rittal – The System.

Faster – better – everywhere.



SM 2384.040

Pushbutton Housings

State: 2025-09-07 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.040 - Pushbutton Housings Stainless steel

Switch housing of stainless steel 1.4301, (AISI 304), with Ø 22.5 mm switch cut-outs. Protection category IP 66.

Features

| | |
|-------------------------------------|---|
| Model No. | SM 2384.040 |
| Material | Housing: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish | Housing and cover: Brushed, grain 240 |
| Supply includes | Housing with cover Quick-release fasteners including plastic bushings |
| Protection category NEMA | NEMA 4X |
| Protection category IP to EN 60 529 | IP 66 |
| IK code | IK08 |
| Dimensions | Width: 280 mm Height: 100 mm Depth: 90 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Hole pattern | 60 mm |
| Breakouts (number x Ø) | 4 x 22.5 mm |
| Lock | Lock version: Quick-release fasteners including plastic bushings No. of locks: 4 |
| Cable entry (quantity x diameter) | 4 |
| No. of metric knockouts | 4 |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 1.4 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 1.501 |
| Customs tariff number | 94039910 |
| EAN | 4028177529441 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|