

# Rittal – The System.

Faster – better – everywhere.



## FT 2736.540 System Window

State: 2025-07-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2736.540 - System Window for VX, TS, VX SE

To cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.



## Features

|                     |   |
|---------------------|---|
| Model No.           | FT 2736.540   |
| Version             | 60 section  |
| Product description | Utilized to cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.  |
| Material            | Extruded aluminum section with die-cast zinc corner pieces and single-pane safety glass.  |
| Surface finish      | Base frame: Powder coated on the outside in RAL 7035,<br>Hinge and lock section: Natural-anodized   |
| Value base frame    | Made from single-pane safety glass: high level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Hinge with 180° opening angle, easily inserted. |

# Features

|                                    |  |
|------------------------------------|--|
| Value base frame                   | <p>Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).</p> <p>Readily height-adjustable.</p> <p>Stabilizes the door cut-out.</p> <p>Conceals the cut edge.</p> <p>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.</p> <p>Frame section height 30 mm or 60 mm</p> |
| Protection category IP to EN 60529 | IP 54  |
| Note                               | <p>Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).</p> <p>Not suitable for outdoor installation</p>  |
| Suitable for                       | <p>Enclosure type: VX</p> <p>TS</p> <p>VX SE</p> <p>Width: = 600 mm</p>  |
| Dimensions                         | <p>Width: 500 mm</p> <p>Height: 670 mm</p> <p>Depth: 77 mm</p>   |
| Visible area                       | <p>Viewing window width: 363 mm</p> <p>Viewing window height: 598 mm</p>   |
| Build depth for components (max.)  | 63 mm  |
| Packaging unit                     | 1 pc(s).   |
| Net weight                         | 6.417  |
| Gross weight                       | 6.78   |
| Customs tariff number              | 76101000   |
| EAN                                | 4028177476448  |
| ETIM 9                             | EC002527   |
| ETIM 8                             | EC002527   |
| ECLASS 8.0                         | 27182301   |

# Approvals

---

Certificates

Protection category