Rittal – The System.

Faster – better – everywhere.





SZ 2411.601 Cable gland, polyamide

State: 2025-11-04 (Source: rittal.com/ca-en)



SZ 2411.601 - Cable gland, polyamide

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.601
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Polyamide 6 Seal: CR/NBR
Color	RAL 7035
Protection category IP to IEC 60 529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 22 mm
Thread	M12 x 1.5
Thread length	8 mm
Min. cable diameter	3 mm
Max. cable diameter	6.5 mm
Operating temperature range	-30 °C100 °C
torque	1.8 Nm
Width across flats	15 mm
Dimensions	Thread: M12 x 1.5 Thread length: 8 mm
Type rating according to UL 50E	Type 4X
Packaging unit	50 pc(s).
Net weight	0.05
Gross weight	0.22

© Rittal 2025

Features

Customs tariff number	39269097
EAN	4028177810013
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Approvals	CSA + CSAus UR + C-UR (recognized) VDE
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025 3