

Rittal – The System.

Faster – better – everywhere.



SK 3120.200 Speed Control

State: 2026-06-27 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3120.200 - Speed Control For filter fans and air-air heat exchangers

Temperature-dependent speed control to reduce noise and save energy in part-load operation.

Features

Model No.	SK 3120.200
Product description	Temperature-dependent speed control for noise reduction and energy conservation in part-load operation.
Technical specifications	For mounting on a 35 mm support rail EN 50 022 Phase cross-over with microcontroller Maximum fan output 300 W or 2 A
Supply includes	Speed Control NTC sensor, length 1.80 m
Packaging unit	1 pc(s).
Speed	100 %
Note	Only suitable for use with single-phase AC motors and equipment Not suitable for EC motors
Dimensions	Width: 105 mm Height: 90.5 mm Depth: 60.2 mm
Setting range	20 °C...55 °C
Rated operating voltage	100 V - 230 V
Net weight	0.359 kg
Gross weight	0.39 kg
Customs tariff number	90321020
ETIM 9	EC000256
ETIM 8	EC000256
ECLASS 8.0	27142320

Features

Product description	SK speed control unit , for filter fans and Air/air heat exchanger, 100 - 230 V, WHD: 105 x 90.5 x 60.2 mm
---------------------	---

Approvals

Approvals	UR
Explanations	Declaration of conformity Declaration of conformity UK