

Rittal – The System.

Faster – better – everywhere.



SZ 2411.661

Cable gland, polyamide

State: 2026-07-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.661 - Cable gland, polyamide

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

Features

| | |
|-------------------------------------|---|
| Model No. | SZ 2411.661 |
| Benefits | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables |
| Material | Polyamide 6 Seal: CR/NBR |
| Color | RAL 7035 |
| Protection category IP to IEC 60529 | IP 68 (5 bar, 30 min.) |
| Dimensions | Height: 53.5 mm |
| Thread | M50 x 1.5 |
| Thread length | 18 mm |
| Min. cable diameter | 30 mm |
| Max. cable diameter | 38 mm |
| Operating temperature range | -30 °C...100 °C |
| torque | 12 Nm |
| Width across flats | 60 mm |
| Dimensions | Thread: M50 x 1.5 Thread length: 18 mm |
| Type rating according to UL 50E | Type 1 Type 4 Type 4X Type 12 Type 13 |
| Packaging unit | 5 pc(s). |

Features

| | |
|-----------------------|---|
| Net weight | 0.535 kg |
| Gross weight | 0.541 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | SZ Cable gland, polyamide, size: M50x1,5, for cables ø 30-38 mm |

Approvals

| | |
|--------------|---|
| Approvals | CSA + CSAus UL + C-UL (listed) VDE |
| Explanations | Declaration of conformity Declaration of conformity UK |
