

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2411.871

## Cable gland, brass

State: 2026-05-11 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.871 - Cable gland, brass

Integrated clamping membranes ensure safe tightening and cable-friendly strain relief.

## Features

Model No.	SZ 2411.871
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief that protects the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Protection category IP to IEC 60529	IP 68 (5 bar, 30 min.)
Dimensions	Height: 54 mm
Thread	M63 x 1.5
Thread length	14 mm
Min. cable diameter	34 mm
Max. cable diameter	44 mm
Operating temperature range	-40 °C...100 °C
torque	50 Nm
Width across flats	64 mm
Dimensions	Thread: M63 x 1.5 Thread length: 14 mm
Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packaging unit	1 pc(s).

## Features

---

Net weight	0.48 kg
Gross weight	0.498 kg
Customs tariff number	74198090
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, brass, size: M63x1,5, for cables ø 34-44 mm

---

## Approvals

---

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

---