

Rittal – The System.

Faster – better – everywhere.



SZ 2482.600 Interface flap

State: 2026-05-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2482.600 - Interface flap For earth leakage circuit-breakers

According to the EN 60 204-1 standard, all power circuits with a rated current of ≤ 20 A that supply the outlets in or on machine enclosures must be protected by means of a residual-current device with a rated differential current ≤ 30 mA. Prepared for the installation of commercially available, 2-pole FI/LS circuit breaker.

Features

| | |
|---------------------|--|
| Model No. | SZ 2482.600 |
| Version | Spring terminals max. 2 x 2.5 mm ² , connection at rear |
| Product description | According to the EN 60 204-1 standard, all power circuits with a rated current of ≤ 20 A that supply the outlets in or on machine enclosures must be protected by means of a residual-current device with a rated differential current ≤ 30 mA. Prepared for the installation of commercially available, 2-pole FI/LS circuit breaker. |
| Benefits | Protection against leakage currents and overload Standard-compliant protection as per EN 60 204 The ground fault circuit interrupter can be reset without opening the enclosure Spring mechanism raises the unclosed cover 30°. This makes it impossible to forget to close the cover. |
| Applications | as programmer interface for controllers as maintenance access for networks For temporary connection of additional equipment For quick connection to existing network structures for programming and maintenance of integral components |
| Function principle | The snap fit closure ensures a good seal. The cover can be locked if necessary. |
| Material | Mounting frame: Plastic PBT (black) Plastic flap: Polycarbonate (semi-transparent) |

Features

| | |
|--------------------------------------|--|
| Supply includes | Interface flap, complete, consisting of plastic frame, outlet (VDE), RJ 45 (socket/socket, Cat 5e) and cut-out for ground fault circuit interrupter Knockouts for USB A (socket/socket) provided 3 mm double-bit with insertable rotary knob |
| Mounting cut-out | Width of opening: 117 mm Cut-out height: 91 mm |
| Note | interface flap may only be used when a ground fault circuit interrupter is fitted |
| Dimensions | Width: 131 mm Height: 127 mm |
| Rated operating voltage | 250 V, 1~, 50 Hz/60 Hz |
| Rated current 230 V, 50 Hz | 10 - 16 A |
| Protection category IP to IEC 60 529 | IP 65 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.56 kg |
| Gross weight | 0.569 kg |
| Customs tariff number | 85366990 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Interface flap, complete, mounting frame and interface inserts, with plastic flap, semi-transparent, RJ45, socket modules Germany, knock-out for RDC protective switch |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|