Rittal – The System.

Faster – better – everywhere.





SK 3130.115 TopTherm air-air heat exchanger

State: 2025-10-21 (Source: rittal.com/ca-en)



SK 3130.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

| Model No. | SK 3130.115 |
|---|--|
| Version | wall-mounted |
| Product description | Air-to-air heat exchangers are especially suitable for aggressive environments since the internal and external circuit are completely separated from each other by two air circuits. |
| Color | RAL 7035 |
| Supply includes | Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Fasteners |
| Specific thermal output | 90 W/K |
| Air throughput (unimpeded air flow) | External circuit at 50 Hz: 850 m³/h External circuit at 60 Hz: 945 m³/h Internal circuit at 50 Hz: 850 m³/h Internal circuit at 60 Hz: 945 m³/h |
| Rated operating voltage | 115 V, 1~, 50 Hz/60 Hz |
| Dimensions | Width: 400 mm Height: 1,580 mm Depth: 215 mm |
| Pre-fuse | Miniature circuit-breaker/fuse: 4 A |
| Temperature control | Electronic Control with Digital Display (factory setting +35 °C) |
| Operating temperature range | -5 °C55 °C |
| Protection category IP to IEC 60 529 | Internal circuit, IP 54 External circuit, IP 34 |

© Rittal 2025

Features

| Packaging unit | 1 pc(s). |
|-----------------------|---------------|
| Net weight | 24.1 |
| Gross weight | 24.95 |
| Customs tariff number | 84158300 |
| EAN | 4028177425125 |
| ETIM 9 | EC002514 |
| ETIM 8 | EC002514 |
| ECLASS 8.0 | 27180711 |

Approvals

| Approvals | UR + C-UR (recognized) |
|--------------|------------------------------|
| Explanations | Declaration of conformity |
| | Declaration of conformity UK |

© Rittal 2025 3