


Rittal – The System.

Faster – better – everywhere.



SZ 2500.211 LED system light

State: 2025-08-03 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.211 - LED system light

LED system light - the first light designed especially for enclosures! Advanced LED technology provides even more light into the last recess.



Features

| | |
|----------------------|--|
| Model No. | SZ 2500.211 |
| Version | with socket |
| Benefits | Optimum illumination of the entire enclosure Option of clip-on, screw or magnetic attachment A configuration to suit every application |
| Version | Socket 90° rotating connector Adjustable light distribution |
| Material | Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS |
| Color | Enclosure: RAL 7016 |
| Supply includes | Assembly screws |
| Rated power | 11 W |
| Connection options | Power Supply, 3-pole Through-wiring, 3-pole Door-operated switch |
| Overvoltage category | II |

Features

| | |
|---|--|
| Protection category | II (total insulation) |
| Light – installation type | Screw fastening Clip fastening |
| Rated impulse withstand voltage, phase to earth | 2500 V AC |
| Rated insulation voltage | 300 V AC |
| Installation options | Directly onto the enclosure section with 25 mm pitch pattern |
| Luminous flux | 900 lm |
| Light color | 4000 K (neutral white) |
| Note | Connection accessories should be ordered separately |
| Dimensions | Width: 437 mm Height: 80 mm Depth: 44 mm |
| Operating temperature range | -20 °C...55 °C |
| Outlets | GB (type G, BS 1363) |
| Rated operating voltage | 100 V - 230 V, 1~, 50 Hz/60 Hz |
| Socket version | GB (type G, BS 1363) |
| Protection category IP to IEC 60529 | IP 20 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.5 |
| Gross weight | 0.628 |
| Customs tariff number | 94054990 |
| EAN | 4028177811355 |
| ETIM 9 | EC000321 |
| ETIM 8 | EC000321 |
| ECLASS 8.0 | 27189241 |

Approvals

Approvals

CQC-CCC
ENEC

Explanations

Declaration of conformity
Declaration of conformity UK