

Rittal – The System.

Faster – better – everywhere.



SZ 2565.300

Plastic Cable Gland Plates

State: 2025-12-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2565.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

Features

Model No.	SZ 2565.300
Product description	Just pierce the plastic with a sharp point and pull the cable through.
Material	Plastic to UL 94-V0
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 301 mm Depth: 221 mm
Suitable for	Enclosure type: AX
Gland plate	Size: 5
Protection category IP to EN 60529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1 Type 12
Quantity of cable entries and Ø (mm) min.-max.	30 x 5-11 40 x 10-15 5 x 15-25 2 x 19-34 2 x 26-54 1 x 50-110
Packaging unit	1 pc(s).
Net weight	0.585
Gross weight	0.59
Customs tariff number	39269097

Features

EAN	4028177935730
E-Number Sweden	E3465292
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------