


# Rittal – The System.

Faster – better – everywhere.



## SK 3140.140

### Roof-mounted fan, roof vent

State: 2026-02-09 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# SK 3140.140 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.



## Features

Model No.	SK 3140.140
Version	roof-mounted
Product description	Roof-mounted fan with a high protection category and flexible installation from the inside or outside.
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Radial, rotary current motor
Unimpeded air flow (with pleated filter)	At 50 Hz: 800 m <sup>3</sup> /h At 60 Hz: 853 m <sup>3</sup> /h
Unimpeded air flow (without filter mats)	At 50 Hz: 863 m <sup>3</sup> /h At 60 Hz: 942 m <sup>3</sup> /h
Air flow (with folded filter in roof-mounted fan) with outlet filter incl. fleece filter mat	1 x 3243300: 555/565 m <sup>3</sup> /h 2 x 3243300: 660/685 m <sup>3</sup> /h

# Features

Air flow (without filter in roof-mounted fan) with outlet filter incl. fleece filter mat	1 x 3243300: 575/600 m <sup>3</sup> /h
Rated operating voltage	380 V - 415 V, 3~, 50 Hz/60 Hz 400 V - 480 V, 3~, 60 Hz
Rated power Pel	At 50 Hz: 98 W At 60 Hz: 130 W
Rated current max.	At 50 Hz: 0.17 A At 60 Hz: 0.2 A
Dimensions	Width: 400 mm Height: 133 mm Depth: 400 mm
Installation depth	34.6 mm
Mounting cut-out	Width of opening: 258 mm Depth of opening: 258 mm
Protection category IP to IEC 60529	IP 21 without filter mat IP 54 including pleated filter
Protection category NEMA	NEMA 12
Note	A chopped fiber filter can be used to increase the protection category to IP 55 (see accessories). To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
Service life of fans (L10, 40 °C))	At 50 Hz: 63,500 h At 60 Hz: 61,500 h
Operating temperature range	-20 °C...55 °C
Storage temperature range	-40 °C...70 °C
Noise pressure level	At 50 Hz: 56 dB(A) At 60 Hz: 58 dB(A)
Packaging unit	1 pc(s).
Net weight	6
Gross weight	6.02
Customs tariff number	84145915

# Features

---

EAN	4028177709133
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

---

# Approvals

---

Approvals	CSA IEC CB 30 - KC Korea TÜV-certified safety UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

---