

Rittal – The System.

Faster – better – everywhere.



SK 3128.100

TopTherm air-air heat exchanger

State: 2026-05-13 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3128.100 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3128.100 |
| Version | wall-mounted |
| Product description | Air-to-air heat exchangers are especially suitable for aggressive environments since the internal and external circuit are completely separated from each other by two air circuits. |
| Color | RAL 7035 |
| Supply includes | Complete unit ready for connection Plug-in terminal strip Floating fault signal contact in case of overtemperature Drilling template Fasteners |
| Specific thermal output | 45 W/K |
| Air throughput (unimpeded air flow) | External circuit at 50 Hz: 600 m ³ /h External circuit at 60 Hz: 625 m ³ /h Internal circuit at 50 Hz: 600 m ³ /h Internal circuit at 60 Hz: 625 m ³ /h |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Rated current max. | At 50 Hz: 0.6 A At 60 Hz: 0.8 A |
| Dimensions | Width: 400 mm Height: 950 mm Depth: 205 mm |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Temperature control | Electronic Control with Digital Display (factory setting +35 °C) |
| Operating temperature range | -5 °C...55 °C |

Features

| | |
|-------------------------------------|--|
| Protection category IP to IEC 60529 | Internal circuit, IP 54 External circuit, IP 34 |
| Packaging unit | 1 pc(s). |
| Net weight | 19 kg |
| Gross weight | 20 kg |
| Customs tariff number | 84158300 |
| ETIM 9 | EC002514 |
| ETIM 8 | EC002514 |
| ECLASS 8.0 | 27180711 |
| Product description | SK Air/Air heat exchanger TopTherm, wall-mounted with controller, 45 W/K, 230 V, 1~, 50/60 Hz, WHD: 400 x 950 x 205 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |