

Rittal – The System.

Faster – better – everywhere.



SK 3138.000

Roof-mounted fan, roof vent

State: 2025-12-10 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3138.000 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.



Features

Model No.	SK 3138.000
Version	roof-mounted
Product description	Roof-mounted fan with a high protection category and flexible installation from the inside or outside.
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	without fan motor
Dimensions	Width: 400 mm Height: 133 mm Depth: 400 mm
Installation depth	27.5 mm
Mounting cut-out	Width of opening: 258 mm Depth of opening: 258 mm
Protection category IP to IEC 60529	IP 21 without filter mat IP 54 including pleated filter

Features

Protection category NEMA	NEMA 12
Note	<p>A chopped fiber filter can be used to increase the protection category to IP 55 (see accessories).</p> <p>To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.</p>
Operating temperature range	-20 °C...55 °C
Storage temperature range	-40 °C...70 °C
Packaging unit	1 pc(s).
Net weight	3.2
Gross weight	3.5
Customs tariff number	84145915
EAN	4028177709188
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	<p>CSA</p> <p>UL + C-UL - FTTA</p> <p>UR + C-UR (recognized)</p>
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>