Rittal - The System.

Faster – better – everywhere.





SK 3140.500 Roof-Mounted Fans

State: 2025-11-18 (Source: rittal.com/ca-en)



SK 3140.500 - Roof-Mounted Fans with EC technology

The new generation of roof-mounted fans (EC version) is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54. The fan may be activated via the control interface with tacho signal output integrated as standard, and monitoring of the fan speed and function is supported.

Features

Model No.	SK 3140.500
Version	roof-mounted EC
Product description	Energy-efficient and powerful roof-mounted fans. The fan may be activated via the control interface with tacho signal output integrated as standard. Also, monitoring of the fan speed and function is supported.
Material	Carbon steel
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Radial, EC motor
Unimpeded air flow (with pleated filter)	At 50 Hz: 976 m³/h At 60 Hz: 976 m³/h
Unimpeded air flow (without filter mats)	At 50 Hz: 1,069 m³/h At 60 Hz: 1,069 m³/h
Air flow (with folted filter in roof- mounted fan) with outlet filter incl. fleece filter mat	1 x 3243200: 690 m³/h 2 x 3243200: 830 m³/h
Air flow (without filter in roof- mounted fan) with outlet filter incl. fleece filter mat	1 x 3243200: 690 m³/h
Rated operating voltage	220 V - 240 V, 1~, 50 Hz/60 Hz

© Rittal 2025 2

Features

Rated power Pel	At 50 Hz: 129 W At 60 Hz: 129 W
Rated current max.	At 50 Hz: 1 A
	At 60 Hz: 1 A
Dimensions	Width: 400 mm Height: 133 mm
	Depth: 400 mm
Installation depth	34.6 mm
Mounting cut-out	Width of opening: 258 mm
-	Depth of opening: 258 mm
Protection category IP to IEC 60	IP 21 without filter mat
529	IP 54 including pleated filter
Protection category NEMA	NEMA 12
Control interface	Yes
Pre-fuse	Miniature circuit-breaker/fuse: 3 A
Note	A chopped fiber filter can be used to increase the protection
	category to IP 55 (see accessories).
	For even more efficient operation or for monitoring the fans, we
	recommend the use of an EC speed control
Service life of fans (L10, 40 °C))	At 50 Hz: 84,000 h
	At 60 Hz: 84,000 h
Operating temperature range	-20 °C55 °C
Storage temperature range	-40 °C70 °C
Noise pressure level	At 50 Hz: 60 dB(A)
	At 60 Hz: 60 dB(A)
Packaging unit	1 pc(s).
Net weight	5.6
Gross weight	5.82
Customs tariff number	84145915
EAN	4028177709126
ETIM 9	EC000320

© Rittal 2025 3

Features

ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA
	30 - KC Korea
	TÜV-certified safety
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025